

# **INFRALED® PRO 25**

Catalog#: PRO-09025

Job Name:

Type:








# Recessed Aimable LED Exam Light for NICU, ICU, & Patient Room

- 25° Tilt, 360° Rotation
- Fully Recessed System
- **Ultimate Infection Control**
- Cool LED Beams, 95+ CRI
- Wall and Remote Controlled
- Adjustable Direction & Intensity Suitable for Dynamic Environments
- 2,523 fc (27,157 lux) on Task (Single Fixture)



**INFRALED® PRO** Configurable remote-aimable lighting

system for healthcare applications



**PRO 60** 

High-angle exam light with 60° beam for Childbirth & Surgery



**PRO 45** 

19" exam light with 45° beam for OR, Hybrid OR, & Cath Lab



#### PRO 35/PRO35V

12" exam light with 35° beam for ICU, Patient Room, ED, & Behavioral




9" exam light with 25° beam for NICU, ICU, & Patient Room



**PRO 25** 



NFRALED" IS A REGISTERED TRADEMARK OF KIRLIN LIGHTING © 2022 KIRLIN LIGHTING





Recessed Aimable LED Exam Light for NICU, ICU, & Patient Room

# PRO-09025

## **Luminaire Specifications (see page 4 for Controls Specifications)**

Luminaires are sold individually, and include the following standard features:



OPTeCOLOR™ LEDs: 95+ CRI, high R9 (72), R13 (96), R15 (96), cool beam, 60,000 hour life (L70). Cyanosis Observation Index of 2.7 meets AS/NZS 1680.2.5



Blue LED indicator strip designates luminaire under active control



BioGard™ anti-microbial white finish, regressed flare trim with tempered clear flat glass lens



IP66 rated, sealed and gasketed trim



Perforation-free, rust and corrosion proof aluminum housing (exceeds 1000hr ASTM salt spray test)

- Up to 25° tilt (from nadir)
- Up to 2,523 fc (27,157 lux) on task
- 0-10V CCR 100-1% dimming
- Input voltage: 110 277V
- Serviceable through aperture; convenient plug-in components for easy installation and service, including 35' RJ45 cable from fixture to wall control.
- Lightweight 18 lbs; complies with OSHPD seismic requirements with addition of safety wires (by others)
- System wattage 37.5W (per luminaire)
- 5 year warranty

# **Options and Ordering Format**

Must Specify		Optional			
Model	ССТ	Trim	Installation	Other Options	
PRO-09025					
	-35K: 3500K, 95+ CRI -41K: 4000K, 95+ CRI	<b>(Blank):</b> White BioGard™ trim, blue LED indicator	(Blank): Suitable for installation in ceiling tile or sheetrock/drywall ceiling	(Blank): None	
	-50K: 5000K, 95+ CRI	-BKBG: BioGard anti-microbial black -94: Custom color; consult factory -94BG: BioGard anti-microbial	-85: Ceiling panel: lays into 2' x 2' grid	-87: Custom length (> 35') wall control cable; consult factory -99: Special modification; consult factory -FS: Single in line fuse	
	custom color finish			-SH: Sealed housing and junction box	


# **Full System Ordering Example**


-	_	•	
Part		Description	Quantity
PRO-09025-41K		INFRALED® PRO 25 Luminaires	2
PRO-WALLC	ACCOUNTS OF THE PROPERTY OF TH	INFRALED® PRO Wall Control Panel	1
PRO-REMOT		INFRALED® PRO Remote Control	1
PRO-SENSR	-	Optional IR Remote Sensor	1

#### PRO-09 025-41K-XX-XX-XX Series Other Options Aperture Size Installation Options Maximum Tilt (Degrees) **Trim Options**

**Color Temperature** 

## **Dimensions**









Drawing

Not to

Scale

Kirlin Lighting | 3401 E. Jefferson Ave., Detroit, MI 48207-4232, USA | P: 313.259.6400 | www.kirlinlighting.com


DUE TO CONTINUING PRODUCT IMPROVEMENTS, KIRLIN LIGHTING RESERVES THE RIGHT TO CHANGE SPECIFICATIONS WITHOUT NOTICE. VISIT WWW.KIRLINLIGHTING.COM FOR THE MOST CURRENT DATA

## PRO-09025


## Recessed Aimable LED Exam Light for NICU, ICU, & Patient Room

# **Single Luminaire Performance**

All configuration and performance data assumes ceiling height of 9.5' and task elevation of 3.5'.



	Angle	Distance to Task	FC on Task	Lux on Task
Performance at Nadir	0°	6'	2,523	27,157
Performance at Max Angle	25°	6.6'	1,889	20,333



	U	
	$\bigcirc$	
Ft.	/ FC \	Dia.
6.0 /	2522.5	0.7
8.0	1418.9	0.9
10.0	908.1	1.2
12.0	630.6	1.4
14.0	463.3	1.7
<u>/ 16.0</u>	354.7	1.9 \


Cone of Light


Cone of Light Key

Ft.: Distance from fixture FC: Footcandles at nadir (0°) Dia.: Circle of light at 50% of FC


Photometric testing by I.T.L. (Boulder, CO); Test No. 93353


# Two Light Configuration - 4,000+ fc Delivered





# Four Light Configuration - 7,500+ fc Delivered







## PRO-09025

#### Recessed Aimable LED Exam Light for NICU, ICU, & Patient Room

INFRALED® PRO 25 is controlled via wall control panel and optional remote control. Each controller supports up to 4 luminaires from the INFRALED® PRO family. Each wall control panel includes an infrared sensor. An optional ceilingmounted infrared sensor is also available. All wall controls, remote controls, and remote sensors must be ordered separately.

## Wall Control Panel (PRO-WALLC) Required

- Full function controls for power, fixture selection. intensity and direction
- Tactile-membranes and smooth surfaces for easy cleaning with isopropyl alcohol and disinfecting agents
- May be located outside of patient room or in a secure remote location. If remote control use is anticipated, add PRO-SENSR option, see below
- Includes infrared receiver for remote control operation
- Magnetic docking station for remote control
- Back box provided by Kirlin
- Add option -ACH (Alternative channel) on wall control when adding an additional wall control in the same room
- 5 year warranty


#### Remote Control (PRO-REMOT)

- Full function controls for power, fixture selection, intensity and direction
- Convenient one hand operation
- Tactile-membranes and smooth surfaces for easy cleaning with isopropyl alcohol and disinfecting agents
- Invisible infrared signal will not interfere with other equipment in the room
- Impact resistant construction
- Loss deterring beeper to remind user to return remote to docking station. Beeper is activated if remote control is not used for, nor returned to dock within 1 hour
- "Write-on" area for marking room number
- 2-AA batteries provided
- Low stand-by current assures long battery life
- Add option -ACH (alternative channel) on remote control when adding an additional remote/wall control in the same room
- Add option -BI (beeper inactive) when wishing to add a silence function to the remote
- Add PRO-SENSR (below) when wall control is located outside of patient room or obstructed from remote control's IR signal
- 1 year warranty


# Remote Sensor (PRO-SENSR)

- Optional ceiling mounted infrared sensor enhances signal reception if wall control panel is obstructed
- Each PRO-WALLC supports one PRO-SENSR
- 5 year warranty


## **Wall Control Panel** (PRO-WALLC)



## Remote Control (PRO-REMOT)



## **Ceiling Mounted Infrared Sensor** (PRO-SENSR)









Declare.